

# TWIST&GO

## patented technology

Custom cap design allow using a single bottle for both storing and mixing the product without using jugs or other containers.



## 5 steps

**Five simple steps** for an innovative mixing system.

**Component quantities are preset**, to ensure a **correct, error- and waste-free application**, maximizing product yield.



# The **one and only** **two-component** gel in one single bottle

**Etelec** and **MP One®**, **quality, research** and **innovation**, that will **change** the way you work.

Etelec always chooses **nature** and today, with **MP One®**, even more forcefully by **eliminating** production of additional **containers to be disposed of**, such as bottles, jugs and palettes for mixing and opting for **cardboard packaging** made from **100% recycled** materials and **100% recyclable**, which becomes the real protagonist together with the content.

With **MP One®**, removing means adding.

Adding awareness of a responsible and conscious choice, placing **nature in the foreground**, in everything and for everyone.



DISCOVER MORE





## Single-bottle two-component re-enterable gel filler for electrical insulation



### TWIST&GO Patented technology

The special MPone® cap makes it possible to use a single bottle to store and mix the gel without the use of jugs or other containers

### APPLICATIONS

- Filling of junction boxes
- Insulation of electrical connections
- Insulation of electronic boards and components
- Protection of connections against weathering (rain, moisture), against dust and intrusion of animals, bugs and leaves



### KEY FEATURES



- **Twist&Go patented technology**
- Maximum practicality and rapidity of use
- **Suitable for use in challenging installation conditions** (ladders, decks, scaffolding) and when there is no support surface for product mixing
- Error-free (the quantities of the two components are preset)
- Extra fast cross-linking
- **Eco-friendlier:**  
fewer containers and packaging to dispose of (bottles, jug, stirring stick)
- All the key features that have made MPgel® a successful product

Curing time at 23 °C  
8 minutes

Dielectric strength  
25,5 kV/mm

Colour  
light blue

Operating temperature range  
-60 °C / +200 °C



Compliant to EU  
Directive 2015/863  
(RoHS 3)



Halogen free



Eco-friendly



Non hazardous EU  
Reg. 1272/2008 (CLP)

## Twist and Go Technology

|                                                                                                                                                                                                                                                                         |                                                                                                                                                                                                              |                                                                                                                                                                                                                                            |                                                                                                                                                          |                                                                                                                                                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>1</b></p> <p>Remove the white tear-off safety ring that prevents accidental opening of the capsule containing the second component, which also guarantees product integrity</p>  | <p><b>2</b></p> <p>Screw the top yellow cap all the way on. Check that the blue component is released into the bottle</p>  | <p><b>3</b></p> <p>Shake the bottle for 15 seconds to obtain an even blue mixture that can be checked through the MIXING COLOR CHECK display window</p>  | <p><b>4</b></p> <p>Unscrew the cap completely to open the bottle</p>  | <p><b>5</b></p> <p>Pour into the enclosure to be filled</p>  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|

## Something less, so much more.

Etelec always chooses **nature** and today, with **MP One®**, even more forcefully by **eliminating** production of additional **containers to be disposed of**, such as bottles, jugs and palettes for mixing, and opting for **cardboard packaging** made from **100% recycled** materials and **100% recyclable**.

With **MP One®**, removing means adding.

Adding awareness of a responsible and conscious choice, placing **nature in the foreground**, in everything and for everyone.



## Available sizes

|                                                                                     | ref.  | item       | package (litres) | min./mult. ord.qty (pk) | watch video                                                                           |
|-------------------------------------------------------------------------------------|-------|------------|------------------|-------------------------|---------------------------------------------------------------------------------------|
|  | MP103 | MP One 300 | 300 ml           | 12                      |  |
|                                                                                     | MP106 | MP One 600 | 600 ml           | 12                      |                                                                                       |
|                                                                                     | MP109 | MP One 900 | 900 ml           | 12                      |                                                                                       |